



# i3 Inground – durable and discreet illumination

## i3 Inground

Hadco's I3 Inground luminaire is a line voltage fixture ideal for landscape application. It includes a composite body and trim ring. The I3 is available in incandescent, HID, CF and LED sources with an optical system that allows 15° lamp articulation either side of vertical and 358° rotation without interruption of beam pattern for easy aiming.

### Benefits

- Ensures long-lasting durability
- Creates a variety of effects
- Up to 25,000 hour life with LED module
- High-impact resistance
- Dust-tight, dual-rated, sealed against direct jets of water and continuous immersion

### Features

- Single-piece composite housing includes separate sealed compartments
- Available with a variety of light sources, including LED lamps and modules
- Tempered borosilicate lens
- IP66/68 rated

### Application

- Landscape

## i3 Inground

### Accessories



Ordercode CPS3



Ordercode i3-HHO



Ordercode i3ICL



Ordercode i3SRL

