



i35 Inground - durable and discreet illumination

i35 Inground

The revolutionary i3.5 composite inground provides optimum performance in a small aperture luminaire. Patented design elements including a hinged lens ring, potted factory seal, cool lens option and only 2 screws that do not require a torque wrench - the i3.5 reinforces HADCO's position as the leader in landscape lighting. Now available with LED

Benefits

- Ensures long-lasting durability
- Creates a variety of effects
- Up to 50,000 hour life with LED module
- High-impact resistance
- Dust-tight, dual-rated, sealed against direct jets of water and continuous immersion

Features

- Single-piece composite housing includes separate sealed compartments
- Available with a variety of light sources, including LED lamps and modules
- Tempered borosilicate lens
- IP66/68 rated

Application

- Landscape

Accessories



Ordercode CPS35



Ordercode I35CRGN

