



IL Composite Inground – durable and discreet illumination

IL Composite Inground

The IL Composite Inground luminaire is for low voltage landscape lighting. Its single-piece compression molded fiberglass reinforced polyester composite is factory pressure tested to ensure water will not wick or leak through. It is available in halogen, incandescent and LED. The optical assembly has a clear convex, tempered soda-lime glass and 358° rotation without interruption of the beam pattern.

Benefits

- Design flexibility
- Up to 25,000 hour life with LED
- Ensures long-lasting durability
- Prevents water leaks
- Glare control

Features

- Available with conventional and LED technology
- Offers several color temperatures
- Single-piece composite housing
- Rock guard available
- IP67 rated

Application

- Landscape

IL Composite Inground

Versions

