



Kleenseal 100 - Superior and practical

Kleenseal 100 Recessed Cleanroom LED

The Kleenseal KTR 100 is a cleanroom luminaire well suited for laboratories, fuel storage areas and dirty areas such as locker rooms. Ideal for Class 100-100,000 cleanrooms.

Benefits

- Designed to resist corrosion
- Lightweight
- Speedy installation

Features

- Suitable for wet locations
- Sealed aluminum housing
- Seismic support mounting is standard
- Class 100-100,000 cleanrooms

Application

- Cleanrooms
- Food Processing

Kleenseal 100 Recessed Cleanroom LED

Versions

