



# Kleenseal 200 - Superior and practical

## Kleenseal 200 Recessed Cleanroom

Kleenseal KTR 200 is a hosedown cleanroom luminaire well suited for laboratories, food processing areas, waste water facilities and chemical plants. It can withstand 200 psi hosedown and is NSF listed.

### Benefits

- Designed to resist corrosion

### Features

- Suitable for wet locations
- Sealed aluminum housing with steel optional
- Seismic support mounting is standard

### Application

- Cleanrooms
- Food Processing

### Versions

