



# Kleenseal 300 - Superior and practical

## Kleenseal 300 Recessed Cleanroom

The Kleenseal KTR 300 is a 400 psi hosedown cleanroom luminaire with a sealed junction box, suited for pharmaceutical and chemical facilities, food processing plants or areas requiring hosedown. This unit is NSF listed and suitable for use as raceway (maximum of 4 No. 12 AWG).

### Benefits

- Designed to resist corrosion

### Features

- Suitable for wet locations
- Totally sealed 20ga CRS housing
- Seismic support mounting is standard

### Application

- Cleanrooms
- Food Processing

# Kleenseal 300 Recessed Cleanroom

## Versions

