



L40U – blending traditional luminaire forms with modern lighting function

L40U LED pendant (L40U–STM)

The L40U luminaires feature a one-piece square tapered cast aluminum housing, with a sealed optical system. The cast-aluminum hood includes a photoelectrical hiding decorative finial, assembled on the housing using two built-in hood hinges.

Benefits

- Protected against moisture, dust and insects
- Quick and easy maintenance
- Suitable for a variety of applications

Features

- IP66 rated optical system
- Toolless access to internal components
- Various optics available

Application

- Road and Street

L40U LED pendant (L40U-STM)

Versions

