



# LBD - Quality and high efficiency

## LBD Low Bay

The LBD Low Bay Luminaire offers the highest efficiency for general purpose industrial lighting of any low bay manufactured in the U.S. It is the finest fixture made for mounting heights of 30' and below.

### Benefits

- Easy, positive mounting
- Latches designed to resist corrosion
- Safe relamping

### Features

- Suitable for wet locations
- 3/4" threaded cast aluminum nut and hub
- Heavy wall, one piece die cast aluminum housing
- Stainless steel latches
- One piece injection molded lens

### Application

- Manufacturing
- Industrial

## LBD Low Bay

### Versions

