



# LBN - Quality and high efficiency

## LBN Low Bay

The LBN Low Bay Luminaire offers the high efficiency general purpose industrial lighting for mounting height requirements of 30' and below.

### Benefits

- Easy, positive mounting
- Latches designed to resist corrosion

### Features

- Suitable for wet locations
- 3/4" threaded cast aluminum nut and hub
- Heavy wall, one piece die cast aluminum housing
- Stainless steel latches
- One piece injection molded lens

### Application

- Manufacturing
- Industrial

## LBN Low Bay

### Versions

