



Rugged and sealed

Max-Lite Series Emergency Unit

The Max-Lite Series is sealed and gasketed for areas where oil, water and dust resistance is needed as well as having a rugged thermoplastic housing. Lamp heads may be adjusted to point of the path of egress during a power outage or other emergency.

Benefits

- Designed for protection against moisture
- Designed for increased protection against incidental or intentional abuse

Features

- Constructed of impact resistant, fiberglass reinforced polyester gray housing and includes stainless steel hardware
- Wall mounted unit
- Self powered models feature the Intelli-Charge self-diagnostic circuitry

Application

- Hazardous Location
- Exit and Emergency

Versions

