



Unparalleled design

Round Monopoint Mounts

Die-cast with high-temperature impact-resistant thermoplastic insulator, supporting electrical contacts. Accepts Lytespan luminaires for individual applications. Steel low-profile canopy, attached with two painted slotted cap screws (provided). Crossbar: 0.074 steel, permanently fixed to track. Provides secure mounting of monopoint to electrical junction box. Supply Leads: 16ga. White and Black, Green. insulated stranded wire. Locking Slot: Accepts locking tab of some Lytespan Track luminaires.

Benefits

- Shallow profile allows for clean ceiling

Features

- Ultra shallow Monopoint mounts track fixtures to 3 1/2 or 4" octagon outlet box

Application

- Fashion
- Food and Large Retailers

Versions



6190BK