



Small is the new big

OmniSpot LED Track Heads

OmniSpot LED cylinder is designed to meet the most demanding retail challenges through sleek and discrete aesthetics while providing a high center beam candlepower and efficacy performance. OmniSpot LED cylinder allows for less than 1" of space between the track head and track in the ceiling.

Benefits

- Compact, sleek aesthetic with no visible heat sink
- Excellent beam control with industry leading center beam candlepower up to 30,000
- Very unobtrusive track head at less than 1" of space between the track and track head
- 6 different competitor adapters available, making installation a breeze
- Superior optical control designed for retail

Features

- 4 interchangeable beam spread options: 11°, 18°, 24°, 36°
- Snoot, hex cell, and diffusion films available to customize your lighting needs
- CrispWhite option available to make your colors pop
- Efficacies up to 108 lm/W
- ELV dimming

Application

- Fashion
- Food and Large Retailers
- Office
- Banks
- Hospitality
- Fashion
- Food and Large Retailers
- Office
- Banks
- Hospitality