



OmniSpot with CRI 90 AccuRender: specification grade track heads with LED Color Recipes

OmniSpot LED Track Heads

Our upgraded OmniSpot LED cylinder is now available with Signify's AccuRender technology - a highly efficacious CRI 90. Designed to meet the most demanding retail challenges through sleek and discrete aesthetics, while providing a high center beam candlepower and lighting performance. OmniSpot allows for less than 1" of space between the track head and track in the ceiling, making it a perfect fit for a variety of applications.

Benefits

- Compact, sleek aesthetic with no visible heat sink
- Excellent beam control with industry leading center beam candlepower up to 30,000
- Very unobtrusive track head at less than 1" of space between the track and track head
- Variety of adapters available, making installation a breeze
- Superior optical control designed for retail & hospitality applications

OmniSpot LED Track Heads

Features

- 4 interchangeable beam spread options: 11°, 18°, 24°, 36°
- Snoot, hex cell, and diffusion films available to customize your lighting needs
- LED Color Recipes: CrispWhite, Premium White, and Premium Color options available to make your colors pop
- Efficacies up to 116lm/W
- ELV dimming

Application

- Fashion
- Food and Large Retailers
- Office
- Banks
- Hospitality
- Education


Versions




LLAV11RF



LLAV11RNF



LC20HC



OmniSpot LED Track Heads

Versions

