



Functional, economical

OWL Wraparound LED

The OWL Wraparound LED Linear is the ideal surface mount general illumination luminaire for light commercial and residential applications. The high efficiency LED light engine provides exceptional performance coupled with quality visual light.

Benefits

- Designed to withstand corrosion
- Two mounting options mean flexibility for different needs

Features

- 1% frost acrylic lens shields LEDs from direct view
- Housing is multi-stage phosphate treated
- For ceiling or suspended mounting
- Enclosed lens minimizes penetration of dust, insects and other debris into the lamp compartment

Application

- Manufacturing
- Office
- Banks
- Hospitality

OWL Wraparound LED

Versions



OWL440L835-UNV-DIM

