



R80 - enhancing your project's unique style

Pole (R80)

Made from a seamless 4" round (102 mm) extruded-aluminum shaft welded to a decorative cast-aluminum base incorporating an anchor plate. A 4" by 9" (102 by 229 mm) maintenance opening is complete with cover and copper ground lug. The pole comes with cast-aluminum bolt covers. [~LT~a href="http://www.lumec.com/Lumec3Dv3/home/index_en.php" target="_blank"~GT~](http://www.lumec.com/Lumec3Dv3/home/index_en.php)~LT~b~GT~Lumec3D: Online 3D Configurator~LT~/b~GT~LT~/a~GT~

Benefits

- Built to withstand harsh environmental conditions
- Superior corrosion resistance
- Optimal strength and durability

Features

- Round
- Aluminum construction
- Available in various heights ranging from 8' to 18'

Application

- Bridges, Monuments, Facades
- Road and Street

Pole (R80)

Versions

