



# Enhancing your project's unique style

## Traditional Poles (R90 Series)

Made from a 12 flute, mandrel-formed, aluminum tapered. shaft 6 & 7" round (152 & 178 mm) welded to a 6 5/8" round (168. mm) extruded aluminum pole base which is welded top and bottom. to a cast-aluminum anchor plate. After tapering, forming and welding, the entire shaft assembly is heat-treated to T6 temper. A 4 1/2" by 10" (114 by 254 mm) maintenance opening is complete. with cover and copper ground lug.

### Benefits

- Built to withstand harsh environmental conditions
- Superior corrosion resistance
- Optimal strength and durability

### Features

- Round fluted
- Steel construction
- Available in various heights ranging from 10' to 20'

### Application

- Bridges, Monuments, Facades
- Road and Street

## Traditional Poles (R90 Series)

### Versions

