



Enhancing your project's unique style

Traditional Bottleneck Poles (R800 Series)

Made from a one-piece, seamless 4" round (102 mm) tube of extruded aluminum welded to both the top and bottom of a cast-aluminum anchor plate. A 2" by 4 1/2" (51 by 114 mm) maintenance opening is complete with cover and copper ground lug.

Benefits

- Built to withstand harsh environmental conditions
- Superior corrosion resistance
- Optimal strength and durability

Features

- Round
- Aluminum construction
- Available in various heights ranging from 8' to 20'

Application

- Bridges, Monuments, Facades
- Road and Street

Traditional Bottleneck Poles (R800 Series)

Versions

