



# RA856 - enhancing your project's unique style

## Pole (RA856)

Made from a one-piece, seamless 5 9/16" round (141 mm) tube of extruded aluminum welded to both the top and bottom of a cast-aluminum anchor plate. A 2" by 4 1/2" (51 by 114 mm) maintenance opening is complete with cover and copper ground lug. [http://www.lumec.com/Lumec3Dv2/home/index\\_en.php](http://www.lumec.com/Lumec3Dv2/home/index_en.php) target="\_blank"~GT~LT~b~GT~Lumec3D: Online 3D Configurator~LT~/b~GT~LT~/a~GT~

### Benefits

- Built to withstand harsh environmental conditions
- Superior corrosion resistance
- Optimal strength and durability

### Features

- Round
- Aluminum construction
- Available in various heights ranging from 8' to 22'

### Application

- Bridges, Monuments, Facades
- Road and Street

## Pole (RA856)

### Versions

