



RS856 - enhancing your project's unique style

Pole (RS856)

Made from a one-piece, seamless 5 9/16" round (141 mm) tube of extruded aluminum welded to both the top and bottom of a cast-aluminum anchor plate. A 2" by 4 1/2" (51 by 114 mm) maintenance opening is complete with cover and copper ground lug. [~LT~a href="http://www.lumec.com/Lumec3Dv2/home/index_en.php"](http://www.lumec.com/Lumec3Dv2/home/index_en.php) target="_blank"~GT~~LT~b~GT~Lumec3D: Online 3D Configurator~LT~/b~GT~~LT~/a~GT~

Benefits

- Built to withstand harsh environmental conditions
- Superior corrosion resistance
- Optimal strength and durability

Features

- Round
- Steel construction
- Available in various heights ranging from 12' to 30'

Application

- Bridges, Monuments, Facades
- Road and Street

Pole (RS856)

Versions

