



RTA50 - enhancing your project's unique style

Pole (RTA50)

Made from a 12 flute, mandrel-formed, aluminum tapered shaft 6" round (152 mm) welded to a decorative cast-aluminum base incorporating an anchor plate. After tapering, forming and welding, the entire shaft assembly is heat-treated to T6 temper. A maintenance opening is complete with decorative cast-aluminum cover in the same style as the pole and copper ground lug. [~LT~a href="http://www.lumec.com/Lumec3Dv3/home/index_en.php"](http://www.lumec.com/Lumec3Dv3/home/index_en.php) target="_blank"~GT~~LT~b~GT~Lumec3D: Online 3D Configurator~LT~/b~GT~~LT~/a~GT~

Benefits

- Built to withstand harsh environmental conditions
- Superior corrosion resistance
- Optimal strength and durability

Features

- Round tapered fluted
- Aluminum construction
- Available in various heights ranging from 12' to 18'

Application

- Bridges, Monuments, Facades
- Road and Street

Pole (RTA50)

Versions

