



Enhancing your project's unique style

Contemporary Tapered Poles (TM6)

Made from tapered 6" to 4" (152 by 102 mm) round aluminum shaft welded top and bottom to a cast-aluminum anchor plate. After tapering and welding, the entire shaft assembly is heat-treated to T6 temper. A 3" by 5" (76 by 127 mm) maintenance opening is complete with cover and copper ground lug.

Benefits

- Built to withstand harsh environmental conditions
- Superior corrosion resistance
- Optimal strength and durability

Features

- Round tapered
- Aluminum construction
- Available in various heights ranging from 8' to 20'

Application

- Bridges, Monuments, Facades
- Road and Street

Contemporary Tapered Poles (TM6)

Versions

