



PowerForm – Power and savings just the way you like it

PowerForm LED high output floodlight PFF Gen2

High output lighting doesn't have to mean high energy and maintenance costs. Gardco PowerForm LED site & area and flood luminaires provide your outdoor area with bright, uniform illumination while slashing energy and maintenance costs compared to traditional lighting technologies. Now you can instill a sense of security and attract attention in any large area or floodlighting applications without the hassle of frequent relamping or high utility bills. A wide variety of sizes, optical distributions, mounting options, and industry leading lumen output ranging from approximately 20,000 to 100,000 lumens offer increased flexibility without under- or over-lighting the space.

Benefits

- Combines pole mounted area luminaires and floodlights in one family for a consistent aesthetic look across your outdoor site
- A wide variety of sizes, lumen outputs, mounting options and optical distributions increase flexibility
- Achieves optimal light levels with fewer luminaires compared to traditional 1000W HID solutions
- Further enhance savings through optional controls

Features

- Modular housing, available in 5 sizes offering 2, 3, 4, 5, or 6 LED modules
- Light output ranging from over 20,000 to 100,000 lumens
- Type 2, 3, 4, 5 Wide, and Auto Front Row distributions available
- IP66-rated optical assemblies and electrical housing
- Slipfitter and yoke mount available

PowerForm LED high output floodlight PFF Gen2

Application

- Airports
- Bridges, Monuments, Facades
- Food and Large Retailers
- Industrial
- Infrastructure
- Manufacturing
- Municipal Buildings
- Parks and Plazas
- Ports and Port Authorities
- Recreational Sports
- Security Lighting
- Sign Lighting
- Warehouses

Versions

