



Versatility from the inside out

Refractive post top with LumiLock LED (RL32 / RL52)

Whether you are looking to beautify or add a sense of security and wellbeing to your outdoor space, the highly configurable Hadco LED refractive post tops paired with the latest LumiLock light engine GX4 will definitely help you achieve your goals. A multitude of exterior luminaire styles allow you to create promenades and areas exuding timeless, historical charm both day and night. The configurable LED light engine GX4 is an ideal alternative to HID sources, providing you with significant energy savings, and more choices for light levels, optics and controls.

Benefits

- Highly configurable luminaires, a multitude of luminaire styles
- Provides a quick and simple retrofit solution while maintaining excellent light levels
- Field capabilities to change distribution to adapt when needed
- Provides the right amount of light where you need it
- Simple dimming to state of the art connected lighting solutions to maximize energy savings

Features

- Variety of cages, finials, roofs, pods and colors to customize the project along with various poles and brackets
- Available in Type 3 or Type 5 distributions
- Variety of LED color choices in warm and neutral CCTs
- Variety of drive current, optic, dimming and control choices
- IP66 rated LED Engine

Refractive post top with LumiLock LED (RL32 / RL52)

Application

- Road and Street
- Arena and Sports
- Fountains and Pools
- Bridges, Monuments, Facades
- Road and Street
- Arena and Sports
- Fountains and Pools
- Bridges, Monuments, Facades
- Road and Street
- Arena and Sports
- Fountains and Pools
- Bridges, Monuments, Facades

Versions

