



# Renaissance - designed to exceed

## Renaissance pendant - large (RN20-RN30)

Designed to exceed the aesthetic expectations of city planners, lighting designers, and other outdoor lighting professionals, the Renaissance stands as a tribute to history. The Renaissance mixes refinement together with ambition. The design reflects and evokes late 19th and early 20th century styling and is perfectly suited for most urban and rural areas. The state-of-the-art technology inside provides exceptional photometric performance, a long lifespan, and ease of maintenance. The Renaissance luminaire, now available with the LEDgine platform, offers high output for parking lots and high density street lighting. When powered by LEDgine you can save up to 60% in energy costs. It replaces up to 250W HPS which is equivalent up to 90 lumen per watt. [www.lumec.com/Lumec3Dv3/home/index\\_en.php](http://www.lumec.com/Lumec3Dv3/home/index_en.php) target="\_blank"~GT~LT~b~GT~Lumec3D: Online 3D Configurator~LT~/b~GT~LT~/a~GT~

### Benefits

- Provides design flexibility
- Simple and fast maintenance
- Keeps optics free of contaminants
- Ensures top-level performance in harsh environmental conditions

### Features

- Offers a variety of cages, crowns, and decorative deflectors
- Tool-free access to electrical components
- IP66 optical system
- Constructed from top-quality materials

### Application

- Road and Street
- Bridges, Monuments, Facades