



RFL1 - adding elegance and improved visibility to the low level environment

RFL1 Steplight

RFL1 step light is a low voltage for wall applications. The die-cast aluminum faceplate includes a galvanized steel, single gang recessed box with stainless steel fasteners. A frosted tempered glass lens is included and lamping requires a 12W maximum S-8 (93) lamp.

Benefits

- Durable and lasting construction
- Quick and easy installation
- Fade and abrasion resistant

Features

- Die cast aluminum faceplate with galvanized steel
- Lamp included
- Low voltage quick connector included

Application

- Walkway

RFL1 Steplight

Versions

