



# Serenade - grace in all simplicity, designed for performance and reliability

## Serenade DSX post top (S56)

Inspired by early 20th century styling, the Serenade displays its originality with a pleasant blend of features that merge sturdy construction, aesthetics, and efficiency. The Serenade DSX encompasses a sophisticated reflector and refractor system. Superior efficiency and IES cutoff are two of the many benefits this optical system offers. Having as low as 1% uplight sets the Serenade DSX apart from imitators, while increased efficiency can help reduce energy usage. IP66 sealed optical system keeps the optics free of contaminants, ensuring performance for years to come. [~LT~a href="http://www.lumec.com/Lumec3Dv3/home/index\\_en.php" target="\\_blank"~GT~](http://www.lumec.com/Lumec3Dv3/home/index_en.php)  
~LT~b~GT~Lumec3D: Online 3D Configurator~LT~/b~GT~LT~/a~GT~

### Benefits

- Keeps optics free of contaminants
- Ensures top-level performance in harsh environmental conditions
- Simple and fast maintenance

### Features

- IP66 optical system
- Die-cast aluminum construction
- Tool-free access to internal components

### Application

- Road and Street
- Bridges, Monuments, Facades