



Shine - A family of uniformly luminous fixtures combines Ledalite quality and value.

Shine

A family of uniformly luminous fixtures, Shine recessed delivers outstanding performance for superior energy savings. Available in a wide variety of sizes, Shine is a highly efficient and economical solution for any energy challenged recessed lighting project.

Benefits

- High efficiency with a fully luminous optic, minimizing harsh shadows
- Wide range of fixture sizes
- Most configurations available on 10-day QuickShip
- Accessible from below with lift-and-shift lenses

Features

- Available in traditional 1'x4', 2'x2' & 2'x4' sizes in addition to 20"x2', 20"x4', 600x600mm & 600x1200mm sizes for uncommon grids.
- Drywall Trim Kit available in 1'x4', 2'x2' & 2'x4' sizes
- Multiple lumen packages and color temperatures to meet any specification.
- Interact Ready

Shine

Application

- Office
- Banks
- Hospitality
- Fashion
- Education
- Retail

Versions

