



Smart TriLyte - Reliability and high efficiency

Smart TriLyte

The Smart TriLyte uses the optimum Advance programmed start ballast and Philips Lighting low-mercury Alto II™ T8 lamps or Alto® T5HO lamps within a CFI Fluorescent high-performance TriLyte. TriLyte is already a powerful brand name model in the fluorescent high bay market thanks to the high efficiency, reliability and strength of this full body fluorescent high bay.

Benefits

- LampMaximizer optimizes lamp life and energy costs while reducing maintenance costs
- Provides clean, smooth, installation-friendly corners

Features

- One-piece post-painted housing
- Rated for ballast case temperature up to 90°C

Application

- Office
- Banks
- Hospitality
- Manufacturing
- Arena and Sports

Smart TriLyte

Versions

