



Sleek, compact look

Sof-Tech Line Voltage Track Heads

Sof-Tech features die cast components with silicone rubber for aiming comfort. This series is available in both open back or fully enclosed versions, and two accessories may be used with the appropriate accessory holder.

Benefits

- The minimal silhouette has the look of low voltage without the need for transformers
- These units are engineered to ensure cool operation over the life of the product
- Lamps are slightly regressed to provide better cut-off than typically found in PAR rings

Features

- Integral cross blade louver provide some glare reduction and can accommodate one accessory
- Engineered with vents for heat dissipation to ensure cool operation
- A wide silicone band surrounds the lamp ring and the socket cup is enclosed in a silicone housing to provide a comfortable grip for aiming and relamping

Application

- Fashion
- Food and Large Retailers

Sof-Tech Line Voltage Track Heads

Versions



Accessories



Ordercode LIGU60000321,
LIGU60000322, LIGU60000323

