



SR Strip - Cost Effective

SR Strip Retrofit Kit

The SR strip retrofit kit is designed to offer the end user a cost effective way to increase the efficiency and lumen output of existing strip fixtures. Custom fabricated for the existing channel width, the SR conversion kit is easy to install and provides for high efficiency lighting. Applications include distribution, warehouse, aisle lighting, retail applications and virtually anywhere existing strip fixtures are currently in use. SR retrofit kits are available with a variety of lamp and reflector combinations allowing the customer to design the SR system to meet or exceed existing light levels and customize the "look" to match their specific needs.

Benefits

- Sturdy construction
- Excellent light distribution
- Easy installation and maintenance

Features

- Custom fabricated cold rolled steel housing
- Precision brake formed aluminum reflector
- Entry without tools

Application

- Retail
- Office
- Manufacturing

SR Strip Retrofit Kit

Versions

