



SS Strip - Low profile, industrial styling

SS Staggered T5 Strip

Full 4" overlap. Eliminates shadows from lamp ends. Housing only 1-7/16" deep. Safe-handling metal edges. Fully enclosed wire way. Excellent for applications where continuous, even illumination is required.

Benefits

- Uniform lighting
- Easy installation

Features

- Only 1-7/16" deep
- Utilizes compact, high efficiency, T5 or T5HO lamps
- 3" lamp overlap for even illumination

Application

- Manufacturing
- Office

SS Staggered T5 Strip

Versions

