



SV Strip – Compact, efficient

SV T5 Strip

2" wide T5 Strip Series utilizes compact, high efficiency T5 or T5HO lamps. Options include lengths of 22", 34" and 46" with a full array of accessories that include wireguards, stem kits and reflectors.

Benefits

- Multiple mounting options means flexibility for different needs

Features

- Available in lengths of 2', 3', 4' or 8'
- Channel is only 2" wide and 1-5/8" deep
- Surface, pendant or cable mounting
- Suitable for damp locations

Application

- Manufacturing
- Education

SV T5 Strip

Versions

