



Durable and wet location approved

SVR16 Series Remote Unit

The SVR16 Series is ideal for high abuse areas with a housing and backplate molded from high impact GE Lexan® polycarbonate. The SVR16 is UL Listed wet location standard and includes a gasket kit to prevent water entry.

Benefits

- Aesthetically appealing and designed for architectural excellence
- Designed for increased protection against incidental or intentional abuse
- Designed for protection against moisture

Features

- Housing and backplate are high-abuse and high-impact
- UL wet location standard and tamperproof screw kit
- Snap together backplate and housing

Application

- Exit and Emergency

SVR16 Series Remote Unit

Versions

