



Symmetric Strip - Compact, efficient

Symmetric Series

T5 Strip Series symmetric and asymmetric reflector options. These reflectors come in standard white or specular silver at an overall depth of 1 3/8". Reflector options include solid, slotted and perforated for both of the symmetric and asymmetric designs .

Benefits

- Energy-saving

Features

- Available in lengths of 2', 3', 4' or 8'
- Channel is only 2" wide
- Convenient outlet and switch knockouts provided

Application

- Office
- Banks
- Hospitality
- Education

Symmetric Series

Versions

