



TB361 - elegantly designed for commercial applications

TB361 Bollard

Hadco's TB361 is an elegant bollard designed for commercial application. This line voltage luminaire is available in incandescent, CFL, and HID sources, and is manufactured from high-strength, low-copper, proprietary cast aluminum alloy. Optics include a choice of high performance refractive panels and louvers for a variety of light distributions.

Benefits

- Ensures long-lasting durability and reliability
- Fade and abrasion resistant
- Design flexibility
- Suitable for a variety of applications

Features

- Die cast aluminum housing
- Polyester powdercoat finish
- Available in a variety of lamp technologies
- Variety of optics available

Application

- Arena and Sports
- Bridges, Monuments, Facades
- Security Lighting
- Sign Lighting
- Walkways
- Landscape

TB361 Bollard

Versions

