



TB361 LED - elegantly designed for commercial applications

TB361 Bollard LED

Hadco's TB361 is an elegant bollard designed for commercial application. This LED line voltage luminaire is manufactured from high-strength, low-copper, proprietary cast aluminum alloy. Optics include a choice of high performance refractive panels and louvers for a variety of light distributions.

Benefits

- Ensures long-lasting durability and reliability
- Fade and abrasion resistant
- Offers 50,000 hour life with LED
- Design flexibility
- Suitable for a variety of applications

Features

- Die cast aluminum housing
- Polyester powdercoat finish
- Warm or cool color temperatures available
- Variety of optics available

TB361 Bollard LED

Application

- Arena and Sports
- Bridges, Monuments, Facades
- Security Lighting
- Sign Lighting
- Walkways
- Landscape

Versions

