



# Transit - versatility in action

## Transit Post Top (TR10)

Combining state-of-the-art photometric performance with outstanding ease-of-maintenance the decorative Transit luminaires are designed to last in even the most demanding environments. The versatility and character of the Transit luminaire is clear. Combining stunning good looks with outstanding photometric performance, the Transit incorporates the cutting edge photometrics and ease of maintenance that have made Lumec luminaires the perfect choice for effective area lighting. Equipped with the optional LifeLED the Transit's standard dark-sky friendly full cut-off optics turn this versatile product into one of the most environmentally responsible luminaires available on the market. ~LT~  
[http://www.lumec.com/Lumec3Dv3/home/index\\_en.php](http://www.lumec.com/Lumec3Dv3/home/index_en.php)  
target="\_blank"~GT~LT~b~GT~Lumec3D: Online 3D Configurator~LT~/b~GT~LT~/a~GT~

### Benefits

- Up to 50% energy savings over HID
- Virtually eliminates Luminaire Dirt Depreciation
- Reduced glare
- Offers exceptional performance and cut-off
- Dark-sky friendly

### Features

- IP66 rated Smartseal optical system
- Unique combination of reflectors and internal prism refractors in optical chamber
- Hydro-formed aluminum reflector and tempered glass lens
- Provide full cut-off in five different distributions

### Application

- Road and Street
- Parks and Plazas