



Twilighter LED - dependable security

Twilighter Wall Pack LED

Twilighter Series Wallprism is excellent for security, accent and perimeter lighting. Applications include entrance ways, garages, tunnels, overpasses and alleys. It includes a vandal-resistant polycarbonate housing and aluminum reflector for smooth "down-and-out" distribution. Also available with LED sources for a long life of 50,000 hours.

Benefits

- 50,000 hour life
- Durable and lasting construction
- Excellent energy efficiency

Features

- UV stabilized polycarbonate lens and front housing
- Silicone gasketing
- Excellent thermal management
- Factory-installed photocell
- UL listed for wet location

Application

- Security Lighting

Twilighter Wall Pack LED

Versions

