



Vaporlume - Sealed integrity and high performance

V2 Specification Vaporlume

The Specification Vaporlume is a wet location listed luminaire with a fiberglass reinforced polyester housing, high impact DR acrylic lens and stainless steel cam action latches.

Benefits

- Multiple mounting options means flexibility for different needs
- Smoother exterior surface allows for easy cleaning
- Acceptable for outdoor as well as indoor intallations

Features

- Suitable for wet locations
- IP65 rating standard
- Can be surface (wall/ceiling) or suspended mounted unless otherwise specified
- Non-conductive, non-corrosive housing

Application

- Cleanrooms
- Food Processing
- Petrol and Convenience
- Parking Garages

V2 Specification Vaporlume

Versions

