



Better performance in half the size

Vertilyte Mini

Vertilyte Mini offers the same high-performance as Lightolier's Vertilyte, but comes with an aesthetically pleasing smaller ballast housing. This competitively priced addition to Lightolier's full line of metal halide lamping options replaces the current Vertilyte version (except 100W) and offers the same unique vertical ballast design, maximum energy efficiency, superior colour rendering—CRI of up to 92—and long lamp life. In addition to its compact design, Vertilyte Mini improves ease-of-use with an ON/OFF switch located on the squat adaptor, instead of on the ballast housing. Engineered with an electronic ballast, Vertilyte Mini is ideal for making objects stand out in retail stores, specialty food counters, museums and other commercial/institutional interiors. It is available in white (WH), black (BK) and aluminum (AL) using PAR or ED-17P lamps.

Benefits

- Aesthetically pleasing smaller ballast housing
- Improved ease-of-use with an On/Off switch on the squat adapter
- Ideal for making objects stand out in retail stores, specialty food counters, and museums

Features

- Ridged aluminum housing acts as heat sink for cooler operation
- Compact, durable, and energy efficient electronic ballast
- Vertical rotation up to 180°
- Horizontally adjustable with 350° stop capability

Application

- Office
- Banks
- Hospitality

Vertilyte Mini

Versions

