



Victorian LED - delivering energy savings and longevity with existing lighting infrastructure

Victorian Post Top with EcoSwap LED (VL72)

EcoSwap allows you to switch to LED lighting and have great energy savings and longevity while keeping the same outdoor lighting infrastructure. It is the first and only light engine to offer luminaire thermal analysis conducted inside the luminaire which guarantees the performance and longevity of the LED light engine. For retrofit, EcoSwap offers the most lumen output per watt on the market.

Benefits

- Up to 56,000 hour life
- Maximizes pole spacings
- Excellent uniformity
- Ensures durability in harsh environmental conditions
- Fade and abrasion resistant

Features

- Optimal thermal management
- Composed of high performance acrylic refractor lenses
- Die-cast aluminum construction
- Polyester powdercoat finish

Victorian Post Top with EcoSwap LED (VL72)

Application

- Road and Street
- Arena and Sports
- Fountains and Pools
- Bridges, Monuments, Facades

Versions

