



# VL - Compact, versatile

## VL Vanity Light

The VL fixture is a compact lensed fixture designed for use over vanities. Other applications include stairwells, utility areas, corridors and restrooms. The VL series is a versatile lensed fixture that allows flexibility in design. Other options include emergency battery back-up, center lamp divider and convenience outlet, which further enhance the usability of this economical fixture series. The Linear Prism design of the lens allows for optimal light output and superior distribution.

### Benefits

- Multiple mounting options means flexibility for different needs

### Features

- Manufactured with all the knockouts necessary for standard surface or pendant mounting on the ceiling or wall
- Housing is brake formed from heavy gauge cold rolled steel

### Application

- Exit and Emergency
- Hazardous Location
- Education
- Hospitals and Care Centers

## VL Vanity Light

### Versions

