



# High performance and clean appearance

## Wal-Lyter LED Recessed Wall Wash

The Day-Brite / CFI Wal-Lyter LED Recessed Wallwash is a high performance luminaire luminaire that delivers good light levels and an even wash of light. Low-iridescent semi-specular reflectors do not protrude below the ceiling line. This provides a clean appearance while controlling the light output of high efficiency LED boards to illuminate vertical surfaces uniformly.

### Benefits

- Evenly lights vertical surfaces or displays
- Low maintenance
- Fits all lay-in grid ceiling systems

### Features

- High efficiency LEDs have a minimum of 5, hour rated life
- UL listed access plate
- Easy, quick installation

### Application

- Office
- Banks
- Hospitality
- Fashion

## Wal-Lyter LED Recessed Wall Wash

### Versions

