



# High performance and clean appearance

## Wal-Master Wall Wash

Wal-Master Fluorescent Wall Wash Lensed, Ceiling Recessed: Wal-Master is a high performance wall-washer that delivers an exceptionally even wash of light from the ceiling line to the floor line utilizing TT5 (Biax Type) compact fluorescent lamps. It is much more efficient and more cost effective than most incandescent units producing equivalent illumination. Wal-Master is ideal for highlighting merchandise displays, brightening the walls in offices illuminating with sharp cut-off parabolics and for many other wall lighting applications.

### Benefits

- Evenly lights vertical surfaces or displays
- Requires less maintenance than incandescent
- No edges protrude below grid ceiling systems
- Fits all standard and narrow grid ceiling systems

### Features

- 87% energy savings vs. incandescent
- Ease of maintenance
- Easy, quick installation

### Application

- Office
- Banks
- Hospitality

## Wal-Master Wall Wash

### Versions

