



# WAM1/WBM1 – offers a variety of lighting design possibilities

## WAM1/WBM1 Mini Floodlight

The WAM1/WBM1 landscape flood light is a line voltage luminaire used for general illumination. It's constructed of die-cast aluminum with silicone gasketing. A fully-adjustable swivel arm with vibration-proof locking teeth is used for mounting. Optics include a Clear tempered glass lens or frosted tempered glass lens with 75W T3 or LED source. The LED lamp source delivers 50,000 hours of operating life, has a CCT of 3,000K or 4,000K and a CRI of 80.

### Benefits

- Ensures long-lasting durability and reliability
- Able to direct light with ultimate precision
- Prevents water leaks
- Fade and abrasion resistant

### Features

- Die cast aluminum housing
- Fully-adjustable swivel arm with vibration-proof locking teeth
- Silicone gasketing
- Polyester powdercoat finish
- Clear or frosted tempered lens available

### Application

- Landscape

## WAM1/WBM1 Mini Floodlight

### Versions

