



# SilkSpace delivers discrete, comfortable lighting with great performance and ultra low-glare.

## SilkSpace

Ledalite SilkSpace LED recessed combines LED Light Guide technology and Ledalite's revolutionary MesoOptics technology to deliver discrete, comfortable lighting with great performance and ultra low-glare.

### Benefits

- Fully luminous, minimalist aesthetic superior performance and ultra low-glare.
- Optional controls and sensors
- Wide variety of sizes, lumen packages and color temperatures.

### Features

- Multiple lumen packages and color temperatures
- Available in 1'x4', 2'x2' & 2'x4'
- Optional daylight or occupancy sensors available
- Optional drywall kits available


### Application

- Office
- Healthcare
- Education Assisted Living Retail

## Versions



## Accessories



Ordercode SWZDT

