



Simple, easy, convenient

LSW

LSW Lens Wrap Ceiling/Wall Mounted - Specification Grade For ceiling or wall (vertically or horizontally) mounted applications. Only 3 7/8" deep, meets Americans with Disabilities Act (wall mounted). Low brightness .125 thick linear prismatic virgin acrylic refractor. Invisible spring steel latches align refractor to housing. 2 gauge cold rolled steel post painted baked white enamel end caps. For over mirror, over bed, corridor, stairwell and bulletin board applications.

Benefits

- Multiple mounting option means flexibility for different needs

Features

- Suitable for wall and ceiling mounted applications
- Available in lengths of 2' or 4'
- Can be vertically or horizontally mounted on wall

Application

- Over mirror/over bed
- Corridor
- Stairwell

LSW

Versions

