



Reliable performance, elegant aesthetics, and affordability

ClearAppeal Recessed LED

ClearAppeal Recessed Architectural LED offers smooth brightness across the face of the luminaire and provides excellent visual comfort. Its modern architectural styling complements any space.

Benefits

- Achieve energy efficiency targets and reduce energy-related costs
- Excellent aesthetics and light distribution
- Ease of maintenance

Features

- Reliable performance up to 130 LPW
- Optional occupancy and daylighting sensors
- Standard 0-10V dimming
- Uniform, glare free light distribution

Application

- Office
- Hospitality
- Education

Specifications

Colour Temperature	-, 3500 K, 4000 K
CRI	80
Efficacy	106, 107, 110, 111, 113, 114, 115, 116, 117, 118, 119, 120, 123, 124, 125, 126, 127, 128, 129, 130 lm/W

Fixture Size	1 ft x 4 ft, 2 ft x 2 ft, 2 ft x 4 ft
Luminaire Input Watts	24, 26, 26 W, 30, 32, 32 W, 33, 33 W, 34, 34 W, 35, 35 W, 36, 36 W, 41, 48, 48 W, 69, 70

ClearAppeal Recessed LED

Luminaire Lumens	3000, 3000 lm, 3800, 3800 lm, 4300, 4300 lm, 4500, 4800, 5400, 5400 lm, 7400
------------------	--

Mounting	Recessed / T-Bar / T-Grid
Voltages	347/UNIV V

Versions

