



ELA - redefining expectations of an economy LED luminaire

ELA Area LED

Stonco's ELA luminaires combine low profile style, advanced LED performance and advanced thermal management technology to deliver outdoor area lighting that is as energy efficient and aesthetically pleasing as it is remarkably economical. Versions are available with automatic profile dimming and motion response capability as well.

Benefits

- Withstands even the harshest environmental conditions
- Design provides smooth transition from luminaire to arm
- Removes risk of misaligning the luminaire and pole
- Maintains consistent visual alignment while placing light exactly where its needed
- Excellent thermal management for long life and lasting performance

Features

- Rugged die cast aluminum housing
- Available in mast arm or wall mount configurations
- Extruded arm assemblies include integral guide channels
- Deep integral airways dissipate heat

Application

- Parks and Plazas
- Road and Street

ELA Area LED

Versions




Accessories



Ordercode Prog MR



Ordercode Prog MR Rem



Ordercode Prog MR Optics

