



# CPL12 – beautifully illuminating walkways for safe navigation

## CPL12 Path Light

The Hadco CPL series is a simply-crafted low voltage path light available in two distinctive lighting heads. It includes a die-cast aluminum with twist-lock top for tool-less relamping and Single-piece molded silicone gasket to prevent water, dust, and insect filtration.

### Benefits

- Toolless relamping
- Protected against moisture, dust and insects
- Superior efficiency
- Quick and easy installation

### Features

- Twist-lock top
- Silicone gasketing
- Multi-faceted aluminum reflector
- Low voltage quick connector included
- Optional mounting stake

### Application

- Landscape

## CPL12 Path Light

### Versions

